

New Improved High Density Bags: Scensibles® SecureFit360® Universal Receptacle Liner Bags

Specifications

Item Number: LBSF500HD
Bag Size: 12.5" x 23" with 7.5" strap
Thickness: 12 microns

Material: High Density Polyethylene with built in antimicrobial inhibits growth of odor-causing bacteria on the bag. Fresh fragrance.
Case count: 500 bags
Case weight: 5 lbs.

What's the difference?

Liner thickness/strength

- 53% thinner yet stronger due to proprietary resin

Costs

- Saves money - costs significantly less than the original LBSF500
- More competitively priced to waxed bags

High Density Poly

- More rigid to provide a formed and snug fit
- High density material is easy for cleaning staff to handle
- Made with the highest quality resin in the plastics industry

Color

Frosted to mask contents yet still allows cleaning staff to see and avoid potential needles and other sharps

Heat seal at top and bottom

Wrap around strap has added durability and does not separate, making it appear neater on the receptacle and easier to handle for cleaning staff

Plastic in landfill

60% less plastic to landfill with removal of center die cut and thinner material

Easier installation

Removal of center die cut reduces a step in installation



U.S. Patent Nos. 8,690,429 and 9,957,105

Same Great Features and Benefits

Plastic SecureFit360® liner bags are custom designed with a unique strap that wraps around bottom of wall mount* receptacles to secure in place and totally enclose menstrual waste**.



Liners cover the inside surface to completely contain waste.

The 7.5 inch **wraparound strap** is used as a handle to eliminate the need to reach into receptacles to remove the liner with the contents.



* Can be used with removable bins of stall recessed units and other models.

** Menstrual blood carries the risk of blood-borne pathogens such as Hepatitis, which can survive even dried on the inside and outside of waste receptacles for several days and still be infectious.

Kraft waxed liner bags just don't stand up to the job.



Kraft Waxed Liner Bags vs. SecureFit360® Liner Bags



	Kraft Waxed Liner Bags	SecureFit360® Liner Bags
Fit	Easily collapse resulting in unsanitary unsafe condition	Totally covers inside surface to contain waste
Safety of Custodians <small>Note: OSHA guidelines expect receptacles be properly lined to protect from physical contact with discarded menstrual waste</small>	Requires custodians to reach into receptacle to remove liner and contents. Increases risk of contact with infectious blood and body fluids (entering body through mouth, nose, eyes and skin) and needle stick injuries.	Wraparound strap secures bag in place and is used as a safety handle to remove liner with contents. Ensures safer emptying practices.
Odor Control	None	Built in antimicrobial inhibits growth of odor-causing bacteria on the bag. Fresh fragrance.
Environmental Impact	Takes more energy to create pulp and manufacture paper. Coated with petroleum-based paraffin which does not degrade in landfill.	New HD SecureFit sends 50% less material weight to landfill than Kraft bag
Case weight	7.10 pounds	5 pounds (lowers shipping cost)

Scensibles® SecureFit360® Universal Poly Receptacle Liners fit EVNT-CWR, CDSS, CDWM, 250-201W, ND-1E, ND-1W and most common surface or wall mount receptacles.

See reference guide to match common receptacles with compatible Scensibles® liners

